

TPS 80/80H

TURBO PUMPING STATION

涡轮分子泵组

The perfect vacuum solution of turbo pump and scroll pump make an ultimate pressure of up to 2×10^{-5} Pa. Specially suitable for oil contamination-free and ultra clean processes. With compact design and two kinds of orientation flange that is available for the widest range of applications. We offer touch panel control unit and the way "Plug and Play". You can also control the TPS 80/80H by the computer with Ethernet cable.

涡轮分子泵和无油干泵的完美配合，最高为 2×10^{-5} Pa 的极限压强。适用于对真空系统无污染和高洁净需求的场景。结构紧凑，两种泵口方向类型，方便不同应用场合。标配触摸屏控制，即插即用，同时预留网络通讯接口，方便采用电脑互联组网控制。



Compact!

紧凑!

Plug and Play!

即插即用!

Oil free!

无油!

SuPro Instruments LTD

速普仪器

Nanshan ,

Shenzhen, China



[Http://www.suproinst.com](http://www.suproinst.com)

Tel: 86-755-26642901

Fax: 86-755-26419205

Email: sales@suproinst.com

技术规格	参数
型号	涡轮泵机组TPS80（泵口垂直方向），TPS80H（泵口水平方向）
分子泵入口法兰	DN 63 ISO -K（标准），LF或CF（可选）
分子泵抽速	65 L/s（N ₂ ）
前级泵	干泵（标准），隔膜泵（可选）
前级泵抽速	0.3 L/s（标准），1.5 L/s（可选）
极限真空	<2*10 ⁻⁵ Pa（泵口）
分子泵工作压强	建议<1 Pa（长时间运行）
泵组启动时间	<120 s
分子泵转速	72000rpm
真空规	德国Leybold Vacuum复合规（标配）
操作方式	德国Beckhof触摸屏控制，可网络外接电脑控制（配套软件）
重量	~20kg
尺寸	450长*400宽*345高（TPS80），450长*440宽*305高（TPS80H）
电源	220V AC，50/60Hz 接地三脚插头
功耗	~200 W
冷却方式	风冷
质量保证	一年免费/终身维护
备注	以上所列技术规格与参数更新恕不另行通知，如有疑问请联系我们



深圳市速普仪器有限公司

地址：深圳市南山区桂庙路22号向南瑞峰B2009

电话：0755-26642901 传真：0755-26419205

邮件：sales@suproinst.com

Http://www.suproinst.com

淘宝店：速普仪器

深圳市速普仪器有限公司（北京办事处）

地址：北京市丰台区丰台镇北大街北里甲1号8幢302

电话：010-63839091 传真：010-63839091

邮件：zkchang@suproinst.com