

FST5000

FILM STRESS TESTER

Based on the principles of the classical substrate curvature method (Stoney formula), and utilizing advanced laser scanning and detection techniques, along with intelligent operation, the FST5000 thin film stress tester is particularly well-suited for measuring and calculating bow height, warpage, profile morphology, radius of curvature, and film stress of wafer-like photonic film samples.

Dual-wavelength Scanning

Fully Automatic

Measurement

High Cost-effectiveness

SuPro Instruments LTD

Shenzhen, China

Tel: 86-755-26642901

Fax: 86-755-26419205



Technical Specifications	Parameters
Basic Principle	Laser curvature method based on Stoney's formula
Measurement Method	Utilizes dual-wavelength lasers for sample scanning measurement Wavelengths: 635nm / 670 nm, >5mW
Main Function	Automatically measures wafer sample contour, sag height, curvature, radius of curvature, and film stress.
Film Stress Testing Range	1~10000 MPa
ROC Testing Range	2-20000m
ROC Reproducibility	<1 % 1σ (ROC < 20 m) <2.5 % 1σ (ROC < 200 m)
Minimum Scanning Step	0.1 mm
Sample Size	Model M6: Max. 6 inches, downward compatible with 4, 3, 2 inches Model M8: Max. 8 inches, downward compatible with 6, 4, 2 inches Model M12: Max. 12 inches, downward compatible with 8, 6, 4 inches
Sample Stage	Electrically rotating stage
Sample Substrate Correction	Capable of correcting raw surface irregularities through data processing (for subtractive mode)
Power Supply	110-220 VAC & 200 Watts Maximum
Communication Interface	USB 3.0
Operating Temperature	Room temperature
Operating Software:	Visualizes 2D/3D display of wafer contour, sag height, curvature radius, and film stress distribution. Window interface/Compatible with Windows 10 system
Operating Computer	Standard branded desktop all-in-one: Display: ≥21 inches, ≥8 GB memory, CPU ≥ 2.5 GHz, ≥512 GB hard disk
Dimension	850mm * 550 mm * 450mm
Weight	35Kg
Warranty	One year
Remarks	The above-listed technical specifications and parameters are subject to up dates without further notice. Contact us if you have any questions.



Shenzhen SuPro Instruments Co., Ltd

Address: B2009, Ruifeng Entrepreneurship Center, Nanshan District, Shenzhen, Guangdong, China

Telephone: + 86-755-26642901 Fax: + 86-755-26419205 E-mail: sales@suproinst.com Http://www.suproinst.com